


RECOMMENDED PANEL CUTOUT

- NOTES:
1. ALL DIMENSIONS IN MM
  2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
  3. TERM. NOS. FOR REFERENCE ONLY.
  4. RATING: 1A @125VAC, 0.5A @250VAC
  5. CONTACT RESISTANCE: 10mILLI-OHMS
  6. DIELECTRIC STRENGTH: 1000 VAC-1Minute
  7. MATERIALS:  
HOUSING: ZINC ALLOY DIE CAST  
CYLINDER: ZINC ALLOY W/CHROME PLATING  
TERMINAL AND CONTACTS: SILVER PLATED
  8. KEYS (2): ZINC ALLOY, CHROME PLATING  
KEYLOCK, KEYS, AND HEX NUT TO BE PACKED TOGETHER IN INDIVIDUAL BAGS.

LEGEND  
⊙ = INDICATES KEY PULL POSSIBLE



| SWITCH FUNCTION | POS 1 | POS 2 |
|-----------------|-------|-------|
| DFE             | ←     | →     |
| DN              |       |       |

| REV. | ECN No. | DESCRIPTION             | DATE     | CHKD |
|------|---------|-------------------------|----------|------|
| C    | 17993   | ADD NOTE 8              | 3/3/08   | RC   |
| B    | 12174   | REVISED SCHEMATIC       | 5/22/02  | CJB  |
| A    | 11732   | RELEASED FOR PRODUCTION | 10/11/01 | CJB  |

| SCALE | DATE     | DR  | DWG     | REV |
|-------|----------|-----|---------|-----|
| 1.5:1 | 10/11/01 | CJB | K400101 | C   |



K0131A102

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED