

Fluke 289 FlukeView® Forms Combo Kit

Technical Data

Now compatible with Fluke Connect™ Mobile App

Maximize productivity with the combined Fluke 289 and FlukeView® Forms Combo Kit. With built-in data logger and TrendCapture capability, the 289 helps you track down elusive, intermittent problems, monitoring equipment with any of its functions while you do other jobs. Using FlukeView Forms software allows you to overlay your logged data from six meters or six time periods to find cause and effect relationships or for condition monitoring. Turn your data into meaningful graphs and tables for a professional report or analyze individual readings or series of measurements. The 289 is compatible with the new Fluke ir3000 FC Infrared Connector, allowing you to share live measurements on your iOS or Android smart device with the Fluke Connect mobile app. The 289/FVF combo kit gives you a practical and affordable approach to predictive maintenance.

Fluke-289/FVF Kit includes:

- Fluke-289 True-rms Industrial Logging Multimeter with TrendCapture, LoZ, LoPass filter, and Lo Ohms
- FVF-SC2 FlukeView Forms Software and cable
- TL71 Silicon Test Lead Set
- AC175 Alligator Clips
- 80BK-A Integrated DMM Temperature Probe
- TPAK Magnetic Meter Hanger for handsfree operation
- C280 Soft Case for meter protection and accessory storage
- Amp Jack Plug Set
- Requires Fluke ir3000 FC Infrared Connector for Fluke Connect communication (not included in FVF Kit)





See it. Save it. Share it. All the facts, right in the field.

Fluke Connect with ShareLive™ video call is the only wireless measurement system that lets you stay in contact with your entire team without leaving the field. The Fluke Connect mobile app is available for Android™ (4.3 and up) and iOS (4s and later) and works with over 20 different Fluke products—the largest suite of connected test tools in the world. And more are on the way. Go to the Fluke website to find out more.

Make the best decisions faster than ever before by viewing all temperature, mechanical, electrical and vibration measurements for each equipment asset in one place. Get started saving time and increasing your productivity.

Download the app at:





Smart phone not included with purchase.





Additional functions/features	Fluke 289	
Multiple on screen displays	Yes	
LoZ	Yes	
50 ohm range	Yes	
Filter for measurements on motor drives	Yes	
True-rms ac bandwidth 100 kHz		
dBV/dBm Yes		
DC mV resolution	1 μV	
Megohm range	up to 500 MΩ	
Conductance	50.00 nS	
Continuity beeper	Yes	
Temperature (°C and °F)	-200 °C to 1350 °C	
Battery/fuse access	Yes/Yes	
Elapse time clock	Yes	
Time of day clock	Yes	
Min-Max-Avg	Yes	
Frequency	Yes	
Duty cycle/pulse width	Yes	
Info button on board help	Yes	
Hold	Yes	
Isolated optical interface	Yes	
Auto/touch hold	Yes	
Reading memory	Yes	
Log to PC	Yes	
On board logging with TrendCapture	Yes	
Logging memory up to 15,000 readi		



289 specifications

•		
Function	Range and resolution	Basic accuracy
DC volts	50.000 mV, 500.00 mV, 5.0000 V, 50.000 V, 500.00 V, 1000.0 V	0.025 %
AC volts		0.4 % (true-rms)
DC current	500.00 μA, 5000.0 μA, 50.000 mA, 400.00 mA, 5.0000 A, 10.000 A	0.05 %
AC current		0.6 % (true-rms)
Temperature (excluding probe)	-200.0 °C to 1350.0 °C (-328.0 °F to 2462.0 °F)	1.0 %
Resistance	50.000 Ω (289 only), 500.00 Ω, 5.0000 kΩ, 50.000 kΩ, 500.00 kΩ, 5.0000 MΩ, 50.00 MΩ, 500.0 MΩ	0.05 %
Capacitance	1.000 nF,10.00 nF 100.0 nF, 1.000 μF, 10.00 μF, 100.0 μF, 100.0 μF, 100.00 mF, 100.00 mF,	1.0 %
Frequency	99.999 Hz, 999.99 Hz, 9.9999 kHz, 99.999 kHz, 999.99 kHz	0.005 % + 1

RF connection time (binding time) may take up to $1\ \text{minute}$.

Ordering information

Fluke-289/FVF True-rms Logging Multimeter Combo Kit with TrendCapture

Optional accessories IR3000FC Fluke Connect **Infrared Connector**

Fluke. Keeping your world up and running.®

Fluke Corporation PO Box 9090, Everett, WA 98206 U.S.A.

Fluke Europe B.V.

PO Box 1186, 5602 BD Eindhoven, The Netherlands

For more information call:

In the U.S.A. (800) 443-5853 or Fax (425) 446-5116 In Europe/M-East/Africa +31 (0) 40 2675 200 or Fax +31 (0) 40 2675 222 In Canada (800)-36-FLUKE or

Fax (905) 890-6866 From other countries +1 (425) 446-5500 or

Fax +1 (425) 446-5116 Web access: http://www.fluke.com

©2007-2014 Fluke Corporation. Specifications subject to change without notice. Printed in U.S.A. 3/2014 6002298A_EN

Modification of this document is not permitted without written permission from Fluke Corporation.