

WIRE ACCESSORIES

WIRE

Wire & Cable Markers

Letters or numbers for identification of wiring and component location. Permanent, legible, foolproof. Made of durable, vinyl cloth markers with plastic coating. Adhesion to steel. Resistant to oil, water, abrasions. Service Temperature Rating: 40°F to 250°F. Precut to exact size. Self-adhesive backed.

Retail Part No.	Description
12-2210	Numbers 1-33
12-2211	Numbers 34-66
12-2212	Numbers 67-99
12-2213	Letters A-Z
12-9229	Kit: 3 Strips of 33, Numbers 1-99

1	2		3	4	5	6	7	8	2	10	IJ	E	1	3 1	4 1	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	3	2 :	33			
L	2		3	4	5	6	7	8	2	10	11	11	1	3 1	4 1	15	16	17	18	19	20	21	22	23	24	25	26	27	28	19	30	31	3	12 3	33			
1	2	-	3	4	5	6	7	8	2	10	11	13	1 1	3 1	4 1	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	3	2 1	33			
£.	2	1	3	4	5	6	7	8	2	10	11	B	1 1	3 1	4 1	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	3	12 :	33			
1	2	1	3	4	5	6	7	8	2	10	п	13	1	3 1	4 1	15	16	17	18	19	28	21	22	23	24	25	26	27	28	29	30	31	3	12 :	33			
L	2	1	3	4	5	6	7	8	2	10	11	13	1 1	3 1	4 1	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	13	12 1	33			
																					. 7																	
1	1	в	C	D		5 8	0	; 1	1	ι.	1	ĸ	L	M	N	0	P	0	2 8	1 5	1	U	1	v	1 3	1	2	5. 4	1	. (: 1)	E	F	G	H	1	1
1		B	C C	D D			0	1			1	K	L	M M	N N	0	P	0		1 5	5 7	U	1	v	1 2	1	1 2		1				E	FF	GG	H	1	
1 1		BBB	CCC	D D D			0					K		M M M	NNN	000	PP	000		1 5	5 7		1		1 2								EEE	FFF	GGG	HHH	1	
		8 8 8 8	CCCC	D D D D			000					KKK		M M M	NNNN	0000	PPP	0000			5 7				1 2		2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2 2		1				EEEE	FFFF	GGGG	HHHH	1 1 1	

Flexible Heat Shrink PVC Tubing

Three Thin Wall PVC assortments of black, clear and black and clear tubing in a variety of inside diameters. The shrink ratio on this tubing is 2 to 1, it is fungus resistant and non-corrosive. It is recommended for tightly sealing connectors, tool handles and weather proofing wire splices in insulated wire or cable. It may be shrunk with heat guns, oven, etc. Refills for these assortments listed under the assortment. This tubing meets UL requirements, ASTM D-922, MIL-1-631 Grade C and MIL-1-23053, Grade 5b.

Retail Part No.	Quantity in Assortment	Retail Part No.	Quantity in Refill	Description (10 Different)
12-1080	23			Assortment of Thin Wall HST, as below
	4	12-1040	35	1/16 DIA X 6", Black, Thin Wall HST
	3	12-1042	32	3/32 DIA X 6", Black, Thin Wall HST
	3	12-1044	30	1/8 DIA X 6", Black, Thin Wall HST
	3	12-1046	27	3/16 DIA X 6", Black, Thin Wall HST
	2	12-1048	23	1/4 DIA X 6", Black, Thin Wall HST
	2	12-1050	30	9/32 DIA X 6", Black, Thin Wall HST
	2	12-1052	19	3/8 DIA X 6", Black, Thin Wall HST
	2	12-1054	15	1/2 DIA X 6", Black, Thin Wall HST
	1	12-1056	15	3/4 DIA X 6", Black, Thin Wall HST
	1	12-1058	10	1 DIA X 6", Black Thin Wall HST

Retail Part No.	Quantity in Assortment	Retail Part No.	Quantity in Refill	Description (7 Different)
12-1082	19			Assortment of Thin Wall HST, as below
	4	12-1060	30	1/16 DIA X 6", Clear, Thin Wall HST
	4	12-1062	27	1/8 DIA X 6", Clear, Thin Wall HST
	3	12-1064	25	1/4 DIA X 6", Clear, Thin Wall HST
	4	12-1066	25	5/16 DIA X 6", Clear, Thin Wall HST
	2	12-1068	20	3/8 DIA X 6", Clear, Thin Wall HST
	2	12-1070	15	5/8 DIA X 6" Clear, Thin Wall HST
	1	12-1072	10	3/4 DIA X 6" Clear, Thin Wall HST



Heat Shrinkable Tubing Assortment

Shrinks to half its original size when heated. Use it for insulating terminals, connectors, tool handles and wire splices. Use heat gun, oven or barrel of soldering iron. Assorted sizes and colors. 6" lengths.

Retail Part No.	Quantity in Assortment	Refill Part No.	Quantity in Refill	Description (5 Different)
H3-462	7			Assortment of Thin Wall HST, as below
	1	12-1040	35	1/16 DIA X 6", Black, Thin Wall HST
	1	12-1052	19	3/8 DIA X 6", Black, Thin Wall HST
	1	12-1058	12	1 DIA X 6", Black, Thin Wall HST
	2	12-1062	27	1/8ID X 6", Clear, Thin Wall HST
	2	12-1064	25	1/4ID X 6", Clear, Thin Wall HST



WIRE



WIRE MANAGEMENT



Fig. 2



Fig. 3



Fig. 4

Fig. 5



Fig. 6

Wire Management

Retail Part No.	Figure No.	Description	Length (Inches)	Width (Inches)	Holding Diameter (Inches)	Tensile Strength (Pounds)	Color
34-316-C	1	Nylon Cable Clip	1	3/8	3/8	N/A	Natural
34-380-C	2	Adhesive Mount Locking Clamp	1	1	1/2	12	Black
34-396-C	3	Adhesive Mount Locking Clamp	1	1/2	1/2	12	Black
34-402-C	4	Nylon Cable Clamps	1 1/4	1/2	5/8	N/A	Natural
34-480-C	5	Flat Adhesive Backed Tie Mount	3/4	3/4	N/A	12	Natural
34-482-C	6	Flat Adhesive Backed Tie Mount	1	1	N/A	12	Natural