

JKL LAMP	VOLTS	AMPS	*MSCP	*LUMENS	AVERAGE	FILAMENT
NUMBER	RATED	±10%	±25%	±25%	LIFE HRS.	TYPE
6PSB	6.0	.140	.120	1.51	15,000	C-2F
12PSB	12.0	.170	.478	6.01	12,000	C-2F
24PSB	24.0	.073	.502	6.31	10,000	C-2F
28PSB	28.0	.040	.287	3.61	6,000	C-2F
35PSB	35.0	.040	.300	3.77	5,000	C-2F
48PSB	48.0	.053	.558	7.01	10,000	CC-2F
60PSB	60.0	.050	.717	9.01	7,500	C-13
120PSB	120.0	.025	.359	4.51	5,000	CC-7A

		METRIC	DIMENSIONS A		1	IVI	ſ				
			TOLERANCE UNLI	ESS	e	WY.	<b>COMPON</b>	NENTS COR	PORAT	ION	
			<del> (++++++++++++++++++++++++++++++++++++</del>	OTHERWISE SPECI	FIED	TITLE	T-2 T	ELEPHONE S	LIDE BASE		
H			THIRD ANGLE	2 PL +/- ANSI #5_28mol							
			PROJECTION	ANGLE +/- 0							
В	ADD LAMP NUMBER 35PSB	5/17/01	DRAWN BY	APPV'D BY DA'	TE  :	SIZE		DRAWING			_
Α	CHANGE FILAMENT TYPE ON 60PSB		L. WENGSTROM	QC 5/17/0	01	Α	55335	<sup>NO.</sup> SLIDE	BASE ANSI	#5-28mo	
	RELEASED	8/16/00	CAD DRAWING			SCALE			REVISION	REV.	SHEET
REV.	DESCRIPTION/ECO	APPV'D	- CAD DRAWING -		`					NO. B	4 4
NO.	NUMBER	DATE	MANUAL REVISIONS NOT PERMITTED		D		NONE	DATE 8/16/00	DATE 5/17/01	D	TOFT
								-			