



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	*MSCP ±25%	*LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
6MB	6.0	.140	.12	1.51	20,000	C-2F
24MB	24.0	.073	.50	6.29	10,000	C-2F
28MB	28.0	.040	.29	3.65	5,000	C-2F
48MB	48.0	.053	.70	8.80	10,000	C-7A
60MB	60.0	.050	.73	9.18	7,500	C-2F
120MB	120.0	.025	.32	4.02	10,000	CC-3A

*LAMP RATED ONLY WITHOUT BASE.

METRIC THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0	JKL COMPONENTS CORPORATION			
		TITLE T-2 1/2 MINIATURE TELEPHONE BAYONET LAMP			
DRAWN BY L. WENGSTROM	APPVD BY L.R.	DATE 5/25/10	SIZE A	FSCM NO. 55335	DRAWING NO. TELEPHONE BAYONET T-2 1/2
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE NONE	RELEASED DATE 10/11/00	REVISION DATE 5/25/10
REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE	REV. NO. A	SHEET 1 OF 1	