



Tool Online Catalog

WHERE TO BUY

Select a Category

GO

60000 SERIES INSULATED BELL-MOUTH TERMINALS

[Product Index](#) > [Terminals & Cable Ties](#) > [Terminals](#) > [60000 Series Insulated Bell-Mouth Terminals](#) > C64206

60000 Series Insulated Bell-Mouth - Spade Tongue, 9/64" Hole, 22-18 AWG

- Flared, vinyl insulated sleeve to allow easier insertion of the wire, or wires with extra-heavy-duty insulation.
- Insulation is color-coded to indicate wire size, red for 22-18 gauge.
- 100 pieces per reusable C-Pack.
- With flange.



Buy Now!

Pictured: C63306

Cat. No.	Hole Dia.	Length	Sleeve Color	Stud Size	Weight Per (oz.)	Width	Wire Size
C64206	9/64"	57/64"	red	4-6	.0224	19/64"	22-18

All dimensions are in inches and (millimeters) except where indicated.

Download High-Resolution .jpg photo

Download High-Resolution .eps photo



Back

The downloadable files are compressed in .zip format to save on downloading times. Decompressing .zip files requires applications such as [WinZip](#) for the PC and [Stuffit Expander](#) for the Macintosh.

For questions regarding Klein Tools, please use the [Contact Klein Tools](#) page. For questions regarding Klein Tools' policy regarding the use of this site, please see our [Legal Notice/Privacy Statement](#).