MALLORY Mallory Sonalert Products, Inc. Part #: **Sales Outline Drawing** Revision:

ZA028MDDT8

S	p	e	C	if	i	ca	lti	0	n	S	

Sound Level Category	Medium				
Mode of Operation	Dual Tone 3.5 - 3.4 kHz @ 1.5 WPS				
Voltage Rating	16 to 28 VDC				
Frequency	3300 ± 500 Hz				
Loudness @ 2 FT	75 to 85 dB(A) Typ.				
Current Draw	40mA MAX				
Housing Material	6/6 Nylon, Color: Black				
Storage Temperature	-40° to +80° C				
Operating Temperature	-30° to +65° C				
Panel Mounting	Recommended hole size is 22.5 mm. Thread front will fit standard 22.5mm hole.				
Knurled Nut	Used to attach part to panel. The max recommended torque is 10 in-lbs.				
Weight (Typical)	28 g				
NEMA 3R,4X, & 12	Approved with use of included gasket.				
Options	Please contact factory.				

