

**Specifications:**

Resonant Frequency (Hz)	500 ~ 7000
Impedance ( $\Omega$ )	$8 \pm 2$
Input Power (Watts RMS)	10
Operating Temperature ( $^{\circ}\text{C}$ )	-20 ~ +70
Storage Temperature ( $^{\circ}\text{C}$ )	-30 ~ +80
Housing	ABS 757 UL94HB plastic resin (Color: Black)
Leading Wire	20 AWG
Weight (Grams)	45
Locations	For indoor/outdoor use
Options	For other options contact factory

**Dimensions:** (units: mm)**ROHS Compliant**