

Specifications:

Resonant Frequency (Hz)	350 ~ 7000
Impedance (Ω)	8 \pm 2
Input Power (Watts RMS)	15
Operating Temperature ($^{\circ}$ C)	-20 ~ +70
Storage Temperature ($^{\circ}$ C)	-30 ~ +80
Housing	Aluminum (Color: Gray)
Leading Wire	20 AWG
Weight (Grams)	960
Locations	For indoor/outdoor use (No Salt environment)
Options	For other options contact factory

Dimensions: (units: mm)**ROHS Compliant**