MALLORY Mallory Sonalert Products,Inc. Part #: Sales Outline Drawing

Part #: SC648ANPR

Revision:


Specifications:

| opcomodiono. | |
|-----------------------|--|
| Sound Level Category | Loud |
| Mode of Operation | Fast Pulse @ 2 - 10 PPS |
| Voltage Rating | 10 to 48 VAC |
| Frequency | 2900 ± 500 Hz |
| Loudness @ 2 FT | 91 to 104 dB(A) Typ. |
| Current Draw | 4-26 mA |
| Housing Material | 6/6 Nylon, Color: Black |
| Storage Temperature | -40° to +85° C |
| Operating Temperature | -30° to +65° C |
| Panel Mounting | Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole. |
| Knurled Nut | Used to attach part to panel. The max recommended torque is 10 in-lbs. |
| Weight (Typical) | 1.6 oz (45g) |
| NEMA 3R,4X, & 12 | Approved with use of ACC03. |
| Options | Please contact factory. |

Dimensions: Inches (mm)


ROHS Compliant

PART DIMENSIONS BEFORE CODE DATE 0809 5



NOTE A: TERMINALS-.032 BRASS TIN PLATED, TAPPED FOR #6-32 SCREW. TWO #6-32 NICKEL PLATED BRASS SCREWS INCLUDED. WILL ACCEPT 1/4' QUICK CONNECT. TE B: MOUNTING- REMOVE BLACK PLASTIC NUT AND INSERT THREADED FRONT THROUGH 1.25' HOLE PUNCHED IN PANEL, IF DRIENTATION IS NEEDED, NOTE LOCKING FLATS ON DRAWING, SCREW NUT BACK ON. DO NOT OVERTIGHTEN.

PART DIMENSIONS AFTER CODE DATE 0810 1 LOCKING 1.19±.09 [30.24±2.29]



NOTE A: TERMINALS-0.32 BRASS TIN PLATED, TAPPED FOR #6-32 SCREW, TWO #6-32 NICKEL PLATED BRASS SCREWS INCLUDED, WILL ACCEPT 1/4' QUICK CONNECT. MOUNTING- REMOVE BLACK PLASTIC NUT AND INSERT THREADED FRONT THROUGH 125' HOLE PUNCHED IN PANEL, IF DREINTATION IS NEEDED, NOTE LOCKING FLATS ON DRAWING, SCREW NUT BACK ON. DO NOT OVERTIGHTEN.