3M™ Metal-out Static Shielding Bag SCC 1500

Static Shielding Bag - Metal-out

3M SCC 1500 metal-out static shielding bags are approved by major electronics manufacturers for use worldwide. Our transparent, metallized static shield bag structure is desinged to provide a static safe environment for sensitive electronic devices. This bag also provides low charge retention and rapid static decay. Bags are lot coded for QC traceability. These bags are tested to meet or exceed certain electrical and physical requirements of ANSI/ESD S541, EIA 625, and to be ANSI/ESD S20.20 program compliant.

Specifications

Physical Properties: **Typical Values** Test Method* 3 mils** **Thickness** MIL-STD-3010 1003 Tensile Strength 7700 PSI ASTM D882 Seam Strength >10 lbs ASTM D882

Heat Sealing Conditions: **Temperature** 300°F - 400°F Time 0.6 - 4.5 seconds

Pressure 30 - 70 PSI

Electrical Properties:

Surface Resistivity / Resistance ASTM D257 or ANSI/ESD STM11.11 <10¹² ohms/square <10¹¹ ohms Interior <10¹² ohms/square $<10^{11}$ ohms Exterior

100 ohms Metal Charge Retention <100 volts CPM Static Shielding < 30 volts

FIA 541 Static Shielding < 10 nJ ANSI/ESD STM11.31 Static Decay < 2 seconds MIL-STD-3010 4046

Silicone or Amine Content Not detected **FTIR**

** tolerance +/-15%


Open Top

ZipTop Reclosable



Material Structure

3M SCC 1500 flat and ZipTop static shielding bags are manufactured using a proprietary top coating. The top coating and metal layer provide low charge retention and Faraday Effect shielding of an Electrostatic Discharge (ESD) with the associated electrostatic fields. Polyester dielectric stops the current from ESD. Tribocharging is minimized by the specially processed polyethylene.



Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for one year from time of purchase. 3M MAKES NO OTHER WAR-RANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WAR-RANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.

*This product is not on the Qualified Product Listing under the Defense Standardization Program.

See 3M Data Sheets for these related items:

Humidity Indicator Cards (HIC's)

Desiccant

Vacuum Sealers

Т A T C EET

SCC 1500 Metal-out Static Shielding Bag

PRODUCT

STATIC SHIELDING BAG, OPEN TOP AND ZIPTOP

ITEM NUMBER 150(W")(L")

DATASHEET 1101-B 98-0799-1066-1 3M Electronic Solutions Division 6801 River Place Blvd Austin, TX 78726-9000 US and Canada: 866-722-3736

Fax: 866-722-3735

Intl: 919-718-0000: Fax: 919-774-8174 email: 3Mstaticinfo@mmm.com; www.3Mstatic.com © 3M 2012. All rights reserved


3M is a trademark of 3M Company. All other trademarks herein are the property of their respective owners.



3M™ Metal-out Static Shielding Bag SCC 1500

Static Shielding Bag - open top

W"x L"	P/N	W"x L"	P/N	W"x L" P/N
3 x 5	15035			12 x 16 1501216
4 x 6	15046	8 x 12	150812	12 x 18 1501218
5 x 8	15058	9 x 12	150912	14 x 18 1501418
6 x 8	15068	10 x 12	1501012	15 x 18 1501518
6 x 10	150610	10 x 14	1501014	16 x 24 1501624
6 x 30	150630	10 x 24	1501024	18 x 18 1501818
7 x 15	150715	11 x 15	1501115	18 x 24 1501824



3M™ Metal-out Static Shielding Bag SCC 1500

Static Shielding Bag - ZipTop Reclosable

W"x L"	P/N	W" x L'	' P/N	W" x L" P/N
3 x 5	150Z35	5 x 8	150Z58	8 x 10 150Z810
4 x 4	150Z44	6 x 8	150Z68	10 x 12 150Z1012
4 x 6	150Z46	6 x 10	150Z610	12 x 18 150Z1218

- All standard sizes in-stock/same day shipment.
- Width is measured from inside seam to inside seam.
- Length is measured from the top edge to the bottom fold.
- Opening is in the "width" dimension.
- Custom bag sizes, custom printing, and custom hot stamping are available.
- Most sizes are packed 100 per case.
 Small sizes are packed 1000 or 500 per case.

PRODUCT DATA SHEET

SCC 1500 Metal-out Static Shielding Bag

PRODUCT

STATIC SHIELDING BAG, OPEN TOP AND ZIPTOP

ITEM NUMBER 150(W")(L")

<u>DATASHEET</u> 1101-B 98-0799-1066-1 3M Electronic Solutions Division 6801 River Place Blvd Austin, TX 78726-9000 US and Canada: 866-722-3736 Fax: 866-722-3735

Fax: 866-722-3735

Intl: 919-718-0000; Fax: 919-774-8174
email: 3Mstaticinfo@mmm.com; www.3Mstatic.com © 3M 2012. All rights reserved

3M is a trademark of 3M Company. All other trademarks herein are the property of their respective owners.

