

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0002061202**
Status: **Obsolete**
Overview: standard .062
Description: 1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1787, Female, with Tin (Sn) Plated Phosphor Bronze Contact, Low Engagement Force, 18-24 AWG, Bag

Documents:
[Drawing \(PDF\)](#)

General


Product Family	Crimp Terminals
Series	<u>1787</u>
Application	Power
Crimp Quality Equipment	Yes
Overview	<u>standard .062</u>
Product Name	Standard .062"

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Bag
Plating min - Mating	0.508µm (20µ")
Plating min - Termination	0.508µm (20µ")
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm (.060-.120")
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

Material Info

Old Part Number	1787-(P901)L
-----------------	--------------



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

1787Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Manual Extraction Tool	<u>0011030002</u>
Hand Crimp Tool for Standard .062" Pin and Socket Crimp Terminals, 18-24 AWG	<u>0638191300</u>

Japan

Description	Product #
Hand Insertion Tool	<u>0011020001</u>

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION