



BU-00000-*
Part # color

* 0 - Black	5 - Green
2 - Red	6 - Blue
4 - Yellow	9 - White

TEST LEADS

1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 Page 16



BU-00285
Insulated "Mini-Alligator" Lead Set

- #22 AWG wire, 18" long.
- Jaw opens 1/4" (6.4mm) max.
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

BU-00286
Insulated "Alligator" Lead Set

- #22 AWG wire, 12" long.
- Skin-tight, flexible insulator.
- Jaw opens 7/16" (11.1mm) max.
- [Product Data Sheet](#)
- [Send us your questions about this product](#)




BU-00287
Insulated "Alligator" Lead Set

- #22 AWG wire, 18" long.
- Tinned copper wire.
- Jaw opens 5/16" (7.9mm) max.
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



BU-2929-M-00-*
Unshrouded Banana Plugs On Both Ends-Ultra-Flexible-Silicone

- 413 strands of soft drawn copper inside silicone rubber insulation.
- Nine leaf banana plug construction.
- #18 AWG wire, UL listed to max voltage 3,000V.22 Amp rating.
 - Compatible with:
 - Fluke® 10, 70, and 80 Series DMM
 - Series I and II ScopeMeter®
 - 860 Series Graphical™ Multimeter
 - Hewlett-Packard® HP970A Series
 - Tektronix® DMM250 Series
 - THM 500 Series
- [Product Data Sheet](#)
- [Send us your questions about this product](#)





BU-5656-B-00-0

Insulated BNC Male—Both Ends

- Insulated, nylon housing.
- Nickel-plated brass center contact.
- Tinned copper wire.
- Coaxial cable RG58 50 ohm.
- **Product Data Sheet**
- [Send us your questions about this product](#)

[Contents](#)|[Next](#)

[Home](#)|[Insulated BNCs](#)|[Clips & Insulators](#)|[Insulated Test Accessories](#)
[Accessories & Probes](#)|[Kits](#)|[Cross Reference](#)

©1999-2000 Mueller Electric Company. All rights reserved.
Problems with the site should be reported to the [webmaster](#).