



BU-00000-★  
Part # color

★ 0 - Black    5 - Green  
 2 - Red       6 - Blue  
 4 - Yellow    9 - White

**CLIPS & INSULATORS**



Enlarge

### BU-60U Alligator Clip - 10 Amp

- Steel, standard clip with out barrel construction
- Solder or crimp connection
- 5/16" (7.9mm) max. jaw opening
- Nose width 0.13"
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

### Alligator Clip with Screw - 10 Amp:

BU-60S (Steel)

BU-60CS (Solid Copper)

- A 640 screw eliminates soldering or crimping
- Nose width 0.13"
- Federal spec.: Type TC-I W-C-440B (BU-60CS)
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



Enlarge



Enlarge

### BU-60PR2 Phone Tip Alligator Clip - 10 Amp

- Barrel construction accepts standard phone tip or test prod tip
- Barrel diameter 0.075" (1.9mm) ID
- Nose width 0.13"
- Steel
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

### BU-60HPR-★ Phone Tip Alligator Clip with Acetate Handle - 10 Amp

- Barrel construction accepts standard phone tip or test prod tip
- Barrel diameter 0.075" (1.9mm) ID
- Nose width 0.13"
- Steel
- Available in black, red, yellow, green, blue and white
- 
- 
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



Enlarge

[Insulated BNCs](#) | [Test Leads](#) | [Insulated Test Accessories](#)  
[Accessories & Probes](#) | [Kits](#) | [Cross Reference](#)

©2003 Mueller Electric Company. All rights reserved.  
Problems with the site should be reported to the [webmaster](#).