



BU-00000-\*  
Part # color

\* 0 - Black    5 - Green  
 2 - Red       6 - Blue  
 4 - Yellow    9 - White

**CLIPS & INSULATORS**



**BU-24APN Heavy Duty 25 - Amp Clip (unmarked)**  
**BU-24APS Heavy Duty 25 - Amp Clip (marked positive)**

[Enlarge](#)

- Steel
- Crimp or screw connection
- Rugged teeth on one jaw
- Jaw opens 3/4" (19mm) max
- For battery operated equipment, chargers, trouble lights
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

### Automotive Clip - 40 Amp

**BU-25 (Steel)**

**BU-25C (Solid Copper)**

- Teeth mesh on all 3 sides
- Jaw opening: 3/4" (19mm) max
- Crimp or screw connection
- Federal Spec.: Type PC-4 W-C-440B (BU-25C)
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



[Enlarge](#)

### BU-26-\* Insulator for Heavy Duty and Automotive Clips



[Enlarge](#)

- Vinyl insulator
- Available in black, red, yellow, green, blue, white
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

### Heavy Duty Clip for Battery & Test Work:

**BU-21APN Unmarked, Steel - 50 Amp**

**BU-21APS Marked positive, Steel - 50 Amp**

**BU-21CPN Unmarked, Solid Copper - 100 Amp**

**BU-21CPS Marked positive, Solid Copper - 100 Amp**

- Copper shunt eliminates spring overheat
- BU-21CPN/CPS, removable copper lug - attach to cable
- Crimp, screw, lug connection
- Federal Spec.: Type PCL-1 W-C-440B (BU-21CPN)
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



[Enlarge](#)

[Insulated BNCs](#) | [Test Leads](#) | [Insulated Test Accessories](#)  
[Accessories & Probes](#) | [Kits](#) | [Cross Reference](#)

©2003 Mueller Electric Company. All rights reserved.  
Problems with the site should be reported to the [webmaster](#).