

BU-26101-* Insulated Plug-On Test Prod

- IEC 1010 compliant
- Stainless steel tip (20 Amp)
- Positive contact up to 1000V
- 0.08" (2mm) stainless steel test point
- Mates with shrouded, unshrouded & retractable 4mm banana plugs
- Insulated body; safety shock guard collar
- Mech. connection: 0.16" (4mm) nickel-plated brass banana jack
- Product Data Sheet
- Send us your questions about this product

BU-20434-* Right angle Insulated Plunger Jaw Clip (1000V, 15 Amp)

- · Jaws hold thick wire, cable, ground leads, rails, screw heads
- Fully insulated body; nickel-plated steel
- Depressed plunger and steel jaws extend to 0.48" (12mm) Open to 1" (25mm)
- Mech. connections: 0.16" (4mm) insulated right angle banana jack
- Mates with shrouded, unshrouded & retractable 4mm banana plugs
- Product Data Sheet
- Send us your questions about this product



Enlarge BU-26130-* Ultra Tech Test Prod

- Stainless steel pod tip pierces to 1000 V
- Insulated body with safety shock guard collar
- Slim-line prod design with clear kynar®
- Mech. connections: 0.16" (4mm) nickel-plated brass banana jack
- Mates with shrouded, unshrouded & retractable 4mm banana plugs
- IEC 1010 compliant
- Product Data Sheet
- Send us your questions about this product

BU-65-* (Silicone) Safety Alligator Clip (30 Amp)

- IEC 1010 compliant
- Fully insulated molded from glass-filled nylon
- Plastic shrouds over metal parts
- Rated to 1000V
- Jaw opens 0.75" (19mm)
- Mates with shrouded, unshrouded & retractable 4mm banana plugs
- Product Data Sheet
- Send us your questions about this product



* represents color: 0=Black 2=Red 4=Yellow 5=Green 6=Blue 9=White

Up Test Leads Accessories Oscilloscope Probes Kits

 $\ensuremath{\mathbb{C}}$ 2003 Mueller Electric Company. All rights reserved. Problems with the site should be reported to the <u>webmaster</u>.