5050 Size Flexible LED Strips

Features

- Available in 3 Different Waterproof Ratings Non–Waterproof (IP20) Water Resistant (IP65)
 - Waterproof (IP68)
- Adhesive Back, Peel & Stick (EXCLUDING WP Suffix)
- Available in 2 Different LED Densities
 Standard 16.4 Ft. (5 Meter) Reels
- Standard 16.4 Ft. (5
 RoHS Compliant
- Very Bright and Low Power Consumption
- Dimmable to 6V DC
- Applications Include: Interior Lighting, Ceilings, Shelves, Cabinets, Showcases, Motor Homes, RV's, Boats and Aviation

Specifications

Viewing Angle: 120° Voltage: 12V DC Wattage per Reel: 150 LED Count: 36W 300 LED Count: 72W Operating Temperature: -20° to +50°C Storage Temperature: -30° to +80°C

Ordering Information



NTE Type No.								
Non-Waterproof		Epoxy Water Resistant		Silicon Tube and Epoxy Waterproof			Luminous	WL (nm)
150 / Reel	300 / Reel	150 / Reel	300 / Reel	150 / Reel	300 / Reel	LED Color	Intensity	& CCT (K)
69-53R	69-56R	69-53R-WR	69-56R-WR	69-53R-WP	69-56R-WP	Red	1000mcd	620 – 630nm
69-53A	69-56A	69-53A-WR	69-56A-WR	69-53A-WP	69-56A-WP	Amber	1000mcd	585 – 595nm
69-53B	69-56B	69-53B-WR	69-56B-WR	69-53B-WP	69-56B-WP	Blue	800mcd	455 – 470nm
69-53G	69-56G	69-53G-WR	69-56G-WR	69-53G-WP	69-56G-WP	Green	2000mcd	510 – 525nm
69-53W	69-56W	69-53W-WR	69-56W-WR	69-53W-WP	69-56W-WP	White	15lm	6000 – 7000K
69-53WW	69-56WW	69-53WW-WR	69-56WW-WR	69-53WW-WP	69-56WW-WP	Warm White	15lm	3000 – 3500K
69-53RGB	69-56RGB	69-53RGB-WR	69-56RGB-WR	69-53RGB-WP	69-56RGB-WP	Red/Green/Blue	800mcd	N/A

NOTE: LED strips should not be used in sealed environments or in areas where ambient temperatures are extremely hot.

Dimensions

