

## Housing - HC-B 16-TMQ-65/O1M25G - 1604815

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON sleeve housing B16, with double locking latch, height 65 mm, with support 1x M25, straight conductor exit



### Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	262.88 GRM
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

Height	65 mm
Width	43 mm
Length	94 mm

#### Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Note	For contact inserts HC-B16, BB32, D40, DD72, HS6, M, K
Type	B16
Housing type	Sleeve housings
Locking type	With double locking latch
No. of cable exits	1
Cable exit	Straight
Screw connection	none
Type of the screw connection	1x M25

# Housing - HC-B 16-TMQ-65/O1M25G - 1604815

## Technical data

### General

Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Material lock	Stainless steel, handle: PA
Material grip body interlock	PA-GF
Assembly instructions	For half and full screw connections

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

Approvals

GOST

---

## Housing - HC-B 16-TMQ-65/O1M25G - 1604815

### Approvals

Ex Approvals

---

Approvals submitted

---

### Approval details



### Drawings

Dimensioned drawing

