



Pincode für D-SUB -Kabel

PIN Code for D-SUB Cable

Code PIN pour cable D-SUB

Aderzahl Number of Wires Nombre de fils	X1	X2	Aderfarbe	Wire Color	Couleur du fil	
	1	1	weiss	white	blanc	(WH)
	2	2	braun	brown	marron	(BN)
	3	3	grün	green	vert	(GN)
	4	4	gelb	yellow	jaune	(YE)
	5	5	grau	gray	gris	(GY)
	6	6	rosa	pink	rose	(PK)
9-polig	7	7	blau	blue	bleu	(BU)
9-pos	8	8	rot	red	rouge	(RD)
9 pôles	9	9	schwarz	black	noir	(BK)
	10	10	violett	violet	violet	(VT)
	11	11	grau-rosa	gray-pink	gris-rose	(GY/PK)
	12	12	rot-blau	red-blue	rouge-bleu	(RD/BU)
15-polig	13	13	weiss-grün	white-green	blanc-vert	(WH/GN)
15-pos	14	14	braun-grün	brown-green	marron-vert	(BN/GN)
15 pôles	15	15	weiss-gelb	white-yellow	blanc-jaune	(WH/YE)
	16	16	gelb-braun	yellow-brown	jaune-marron	(YE/BN)
	17	17	weiss-grau	white-gray	blanc-gris	(WH/GY)
	18	18	grau-braun	gray-brown	gris-marron	(GY/BN)
	19	19	weiss-rosa	white-pink	blanc-rose	(WH/PK)
	20	20	rosa-braun	pink-brown	rose-marron	(PK/BN)
	21	21	weiss-blau	white-blue	blanc-bleu	(WH/BU)
	22	22	braun-blau	brown-blue	marron-bleu	(BN/BU)
25-polig	23	23	weiss-rot	white-red	blanc-rouge	(WH/RD)
25-pos	24	24	braun-rot	brown-red	marron-rouge	(BN/RD)
25 pôles	25	25	weiss-schwarz	white-black	blanc-noir	(WH/BK)
	26	26	braun-schwarz	brown-black	marron-noir	(BN/BK)
	27	27	grau-grün	gray-green	gris-vert	(GY/GN)
	28	28	gelb-grau	yellow-gray	jaune-gris	(YE/GY)
	29	29	rosa-grün	pink-green	rose-vert	(PK/GN)
	30	30	gelb-rosa	yellow-pink	jaune-rose	(YE/PK)
	31	31	grün-blau	green-blue	vert-bleu	(GN/BU)
	32	32	gelb-blau	yellow-blue	jaune-bleu	(YE/BU)
	33	33	grün-rot	green-red	vert-rouge	(GN/RD)
	34	34	gelb-rot	yellow-red	jaune-rouge	(YE/RD)
37-polig	35	35	grün-schwarz	green-black	vert-noir	(GN/BK)
37-pos	36	36	gelb-schwarz	yellow-black	jaune-noir	(YE/BK)
37 pôles	37	37	grau-blau	gray-blue	gris-bleu	(GY/BU)
	38	38	rosa-blau	pink-blue	rose-bleu	(PK/BU)
	39	39	grau-rot	gray-red	gris-rouge	(GY/RD)
	40	40	rosa-rot	pink-red	rose-rouge	(PK/RD)
	41	41	grau-schwarz	gray-black	gris-noir	(GY/BK)
	42	42	rosa-schwarz	pink-black	rose-noir	(PK/BK)
	43	43	blau-schwarz	blue-black	bleu-noir	(BU/BK)
	44	44	rot-schwarz	red-black	rouge-noir	(RD/BK)
	45	45	weiss-braun-schwarz	white-brown-black	blanc-marron-noir	(WH/BN/BK)
	46	46	gelb-grün-schwarz	yellow-green-black	jaune-vert-noir	(YE/GN/BK)
	47	47	grau-rosa-schwarz	gray-pink-black	gris-rose-noir	(GY/PK/BK)
50-polig	48	48	blau-rot-schwarz	blue-red-black	bleu-rouge-noir	(BU/RD/BK)
50-pos	49	49	weiss-grün-schwarz	white-green-black	blanc-vert-noir	(WH/GN/BK)
50 pôles	50	50	grün-braun-schwarz	green-brown-black	vert-marron-noir	(GN/BN/BK)

TNR: 102196-00-06/01.09.04 © Phoenix Contact 2004