
SWITCHES ROCKER

2 =

STANDARD ROCKER SWITCHES



5A @ 125V AC, 3A @ 250V AC

500V DC 100 Meg ohm (Min.) 1500V AC for 1 minute

Copper - Silver Plate

DC 2.5V-1A, 20 Meg ohm (Max.)

	ELECTRICAL RATINGS:						
	16A	125-250V AC 65C			UL E45221		
	1HP	30V DC			ι	UL/CSA	
	1/2A	125V AC			UL/CSA		
	10A	125-250V AC 65C			CSA LR10990		
	10 (6)A	10 (6)A 250V AC T100			VDE 75171		
	75A	A Inrush			EN61058-1		
	10A	28V DC			Approvals N/A		
MATERIALS:							
	Body:		Nylon 6.6				
	Actuator:		Nylon 6.6				
	Contact G	ap:	3mm (.118)				
Contact Material: Silver Alloy							
	Part No.	Туре	Action			Actuator	
	30-250	DPST	ON	-	OFF	Black Nylon	
	30-16705	DPST	ON	-	OFF	White Nylon w/Black Legend	

SPECIFICATIONS:

Current Rating:


Dielectric Strength: Contact Material:

Initial Contact Resistance: Insulation Resistance:

0

6.35 (.250) X 0.8 (.030) Tab

ACTUATOR



11.0 (.433) 21.0 (.827)

4.0 (.157)

9.8 (.386)