

**Search Results**

- Evaluate
  - FAQ's
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'HSTT100-48-545'


Your search criteria matched only one product, shown below

**HSTT100-48-545**



- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
  - Cross-linked, UV resistant material improves flame retardancy, chemical, and temperature resistance
- For clear, add "C" to end of part number package suffix (Example HSTT05-48-QC). Contact customer service for additional color information.

Meets Mil Spec AMS-DTL-23053/5 Class 1(Colors), Class 2 (Clear)

Part Number	HSTT10048-545
RoHS CompliancyStatus	Compliant
Part Description	Thin Wall Polyolefin HeaShrink
Material	Flame retardantpolyolefin cross-linked except clear
Color	Yellow/Green
CSA Certified	Yes
Military Specification	AMS-DTL-23053/5 Class 1
UL Recognized	E122770
Length (ft.)	4
Length (m)	1.2
CE Compliant	No
CE Marking	No
FlammabilityRating	Flame Retardant
Max. Recovered I.D. (In.)	.500
Max. Recovered I.D. (mm)	12.7
Min. Expanded I.D(In.)	1.00
Min. Expanded I.D(mm)	25.4
Nominal Diameter Size	1.00
Nominal RecoveredWall Thickness (In.)	.035
Nominal RecoveredWall Thickness (mm)	.9
Pricing Description	Heat Shrink Thin,1"(25.4mm) Dia, Yellow/Green
Shrink Ratio	2:1
Temperature Range	-67°F to 275°F (-55°C to 135°C)
Min. OrderUOM	PC
Min. OrderQty.	5
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.