
## Pomona®

## Model 122505A & 122506A & Assembly **Instructions** Do-It-Yourself Retractable Sheath Banana Plug



#### **FEATURES:**

- Models 122505A and 122506A accepts 18 to 22 AWG wire.
- Ideal for creating a special patch cord length.
- Spring loaded retractable sheath offers versatile use in sheathed and non-sheathed style of banana jacks.

#### **MATERIALS:**

Insulation: Lucel Acetal Polymer (N127)

Contact: Nickel plated brass & Beryllium Copper

#### **RATINGS:**

Operating Voltage: 1500 VRMS per IEC 1010, CAT III

Operating Temperature:  $-10^{\circ}$ C to  $+80^{\circ}$ C

Current: 20 Amperes

#### **ORDERING INFORMATION:**

Model 122505A (Color: Black) Model 122506A (Color: Red)

All dimensions are in inches. Tolerances (except noted):  $.xx = \pm .02"$  (,51 mm),  $.xxx = \pm .005"$  (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA

6/9/99 SY/EH/LS


Sales: 800-490-2361 Fax: 888-403-3360 Technical Assistance: 800-241-2060 S:\Engineering\Release\DataSheets\FlukeDataSheet\d\_Al\_122505A\_6A\_2\_01.doc

Pomona ACCESS 90260 (800) 444-6785 or (425) 446-6010 More drawings available at www.pomonaelectronics.com

# Pomona®

# Model 122505A & 122506A & Assembly Instructions

### Do-It-Yourself Retractable Sheath Banana Plug



#### **ASSEMBLY INSTRUCTIONS:**

- A. Slide clam nut and split collet over wire.
- B. Solder wire to body.
- C. Tighten clam nut.
- D Slide spring over banana plug body.
- E. Slide sheath over banana plug body until snap.

All dimensions are in inches. Tolerances (except noted):  $.xx = \pm .02$ " (,51 mm),  $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA