Technical Data

SCHAFFNER

Multistage general purpose single-phase filter


FN 2060-6/06

Insertion loss

per CISPR 17

C=0.1ohm/100ohm sym

B=50ohm/50ohm asym D=0.1ohm/100ohm asym



Current rating

A at 40°C (25°C)

6 (6.9)


Sample FasTrack

for FN 2060-6/06 samples

[For part numbering and ordering information, <u>click</u> <u>here</u>]

[NB: Specifications subject to change without notice. This electronic document has been carefully checked. However, Schaffner does not assume any liability for errors or inaccuracies]


Simplified electrical schematic



Mechanical information

Dimensions: millimetres || inches [25.4mm=1 inch]

Click <u>here</u> for information on Schaffner's I/O connections



Home © Schaffner 1998. All trade marks and trade names recognised. Please email any comments to Wordsun who maintain this site.