

Choose your language: English(US)

Search Product:

[\[Advanced \]](#)

- ? [Adapters & power supplies](#)
- ? [Batteries & chargers](#)
- ? [Cables & accessories](#)
- ? [Connectors](#)
- ? [Consumer products & pc acc.](#)
- ? [Electronic components](#)
- ? [High-q tools & dmm's](#)
- ? [Led products & lamps](#)
- ? [Light products](#)
- ? [Loudspeakers & pa systems](#)
- ? [Perel tools](#)
- ? [Security products](#)
- ? [Velleman kits & oscilloscopes](#)

[ROHS Info](#)

[SECURITY PRODUCTS](#) > [STROBES FOR HOME SECURITY DEVICES](#) > [MINI STROBE LIGHTS DC 12V](#) >



ELECTRONIC FLASHING LIGHT - RED

Order Code: HAA40R



Features

- ? for alarm systems, discos, personal use, warning in case of danger, etc...

Specifications

- ? lens color: red
- ? long-life xenon tube
- ? protected against polarity reversal
- ? fully sealed and waterproof
- ? power output: 1W
- ? power supply: DC 12V
- ? current consumption: 150mA @ 12VDC
- ? max. current: 180mA @ 13.8VDC
- ? flash rate: 80-100/min.
- ? life expectancy: ± 3 x 1000000 flashes
- ? operation temperature: -40°F to +176°F
- ? black ABS / acrylic cover
- ? dimensions: 2.8"(Ø) x 2.5"
- ? IP rating: IP54
- ? cable length: 17.62" ± 0.39"
- ? screw: M5

Stock Info

- ? Inner carton:
- ? Outer Carton: 100
- ? EAN Barcode: 5410329233419
- ? Packaging: Unknown