

Search Product:

Submit

[[Advanced](#)]

- ? [Adapters & power supplies](#)
- ? [Batteries & chargers](#)
- ? [Cables & accessories](#)
- ? [Connectors](#)
- ? [Consumer products & pc acc.](#)
- ? [Electronic components](#)
- ? [High-q tools & dmm's](#)
- ? [Led products & lamps](#)
- ? [Light products](#)
- ? [Loudspeakers & pa systems](#)
- ? [Perel tools](#)
- ? [Security products](#)
- ? [Velleman kits & oscilloscopes](#)

[ROHS Info](#)

[ELECTRONIC COMPONENTS](#) > [PASSIVE COMPONENTS](#) > [RESISTIVE COMPONENTS](#) > [CARBON FILM RESISTORS](#) > [CARBON FILM RESISTOR SET 1/4W \(RA -SERIES\)](#) >



PACK OF 610 E12 -SERIES RESISTORS

Order Code: K/RES -E12



High-quality carbon film resistors with a connecting wire that is easily soldered.

Features

- ? applications: TV's, audio and video equipment, telephone receivers and communication systems, instrumentation, home appliances, ...

Specifications

- ? quantity: 610 pieces (10 pcs per value)
- ? serie: E12
- ? number of values: 61 (from 10E to 1M)
- ? power rating: 1/4W
- ? operating temperature range: -67°F to +311°F
- ? tolerance: 5%
- ? max. operating voltage: 250V
- ? operating temperature range: -67°F to 311°F
- ? tolerance: 5%
- ? max. operating voltage: 250V

Stock Info

- ? Inner carton: 10
- ? Outer Carton: 100
- ? EAN Barcode: 5410329238391
- ? Packaging: Blister card