

Choose your language: English (US)

Search Product:

[\[ Advanced \]](#)

- [Adapters & power supplies](#)
- [Batteries & chargers](#)
- [Cables & accessories](#)
- [Connectors](#)
- [Consumer products & pc acc.](#)
- [Electronic components](#)
- [High-q tools & dmm's](#)
- [Lamps & led's](#)
- [Led products & lamps](#)
- [Light products](#)
- [Loudspeakers & pa systems](#)
- [Perel tools](#)
- [Security products](#)
- [Velleman kits & oscilloscopes](#)

[ROHS Info](#)[VELLEMAN KITS & OSCILLOSCOPES](#) > [MODULES](#) > [MODULES](#) >

## 8-CHANNEL RF REMOTE TRANSMITTER

Order Code: VM118R



### Features

- 8 addresses allow the use of multiple receivers
- 'all clear'- function
- open-field range up to 50m / 165ft.
- toggle or momentary mode for each key

### Specifications

- power supply: 3 AAA batteries
- 433MHz operation
- 8 digitalkodade kanaler
- rubber keypad
- LED function/mode indication
- FCC approved ID code: NLO8058

### Files

- [Velleman Projects Catalogs: Kits](#)
- [Velleman Projects Catalogs: Modules & instruments](#)
- [Overview of Velleman modules that are equal to D.I.Y Kits: This sheet is usefull when you want to now witch modules you could find in the do-it-yourself range of Velleman Kits and minikits.](#)
- [infosheet: RF projects features, specs & compatibility](#)
- [usermanual: uk - nl - fr - de -es](#)
- [infosheet: FCC authorisation](#)
- [infosheet: R & TTE Declaration of Conformity](#)

## Stock Info

---

- Inner carton:
- Outer Carton: 125
- EAN Barcode: 5410329331061
- UPC Barcode:
- Packaging: Plastic Bag

(C) 2005 Velleman Components N.V.  
[ [Disclaimer](#) ]