

Search Product:

[\[ Advanced \]](#)

- ? [Adapters & power supplies](#)
- ? [Batteries & chargers](#)
- ? [Cables & accessories](#)
- ? [Connectors](#)
- ? [Consumer products & pc acc.](#)
- ? [Electronic components](#)
- ? [High-q tools & dmm's](#)
- ? [Led products & lamps](#)
- ? [Light products](#)
- ? [Loudspeakers & pa systems](#)
- ? [Perel tools](#)
- ? [Security products](#)
- ? [Velleman kits & oscilloscopes](#)

[ROHS Info](#)

[HIGH - Q TOOLS & DMM'S](#) > [SOLDERING STATIONS](#) > [SOLDERING STATIONS WITH CERAMIC HEATER](#) >



## SOLDERING STATION WITH LCD & CERAMIC HEATER 48W 302°F - 842°F

Order Code: VTSSC40NU



### Features

- ? manual temperature setting
- ? LCD display with digital temperature scale
- ? temperature preset on LCD display
- ? with on/off switch
- ? ceramic heating element with temperature sensor
- ? standard tip (incl.): [BITC10N1](#)

### Specifications

- ? max. heater power for soldering iron: 48W
- ? temperature range: 302 - 842°F
- ? low-voltage iron: 24V AC
- ? weight: 3.48lbs.
- ? dimensions: 7.28" x 3.94" x 6.69"
- ? replacement soldering iron: [VTSSC40N/SP](#)
- ? spare bits:
  - ? [BITC10N2](#) 1.0mm
  - ? [BITC10N3](#) 3.0mm
  - ? [BITC10N4](#) 2.0mm

### Files

- ? [EN- FR- NL- ES- DE- PL- IT](#)

### Stock Info

- ? Inner carton:
- ? Outer Carton: 5
- ? EAN Barcode: 5410329319625
- ? Packaging: Box (Carton)