

Choose your language: English (US)

Search Product:

[\[ Advanced \]](#)

- [Adapters & power supplies](#)
- [Batteries & chargers](#)
- [Cables & accessories](#)
- [Connectors](#)
- [Consumer products & pc acc.](#)
- [Electronic components](#)
- [High-q tools & dmm's](#)
- [Lamps & led's](#)
- [Led products & lamps](#)
- [Light products](#)
- [Loudspeakers & pa systems](#)
- [Perel tools](#)
- [Security products](#)
- [Velleman kits & oscilloscopes](#)

[ROHS Info](#)[HIGH-Q TOOLS & DMM'S](#) > [TOOL SETS](#) >

## BIT SET WITH RATCHET SCREWDRIVER - 101 pcs

Order Code: VTTS12



### Features

- handy, all-in-one 101-piece ratchet set
- reversible ratchet handle
- S2 bits
- comes in a handy storage box

### Specifications

- contents:
  - 1" screwdriver bits (95 pcs):
    - Phillips: 2 x PH0, 2 x PH1, 3 x PH2, 2 x PH3
    - flat: 1/8" , 5/32" , 13/64" , 15/64"
    - pozi: PZ0, 2 x PZ1, 3 x PZ2, 2 x PZ3
    - star: T8, 2 x T10, 2 x T15, 2 x T20, 2 x T25, T27, T30, T40, T45
    - security star: T8, T10, T15, T20, T25, T27, T30, T40, T45
    - hex: H1.5, H2, H2.5, H3, H4, H4.5, H5, H5.5, H6mm
    - hex (SAE): H1/16", H5/64", H3/32", H7/64", H1/8", H9/64", H5/32", H3/16", H7/32", H1/4"
    - security hex: 5/64" , 3/32" , 1/8" , 5/32" , 13/64" , 15/64"
    - security hex (SAE): 5/64", 3/32", 7/64", 1/8", 9/64", 5/32"
    - square: S0, S1, S2, S3
    - spanner: 4, 6, 8, 10
    - four-wing: 6, 8, 10
    - tri-wing: 1, 2, 3, 4
    - clutch: 1, 2, 3
    - spline: M5, M6, M8

- adaptors (5 pcs):
  - 1" bit adaptor
  - 2" bit adaptor
  - 2 23/64" bit adaptor
  - wing nut driver
  - 1" coupler
- ratchet screwdriver
- dimensions: 9 1/16" x 5 29/32" x 1 37/64"
- weight: 2.12 lbs

## Stock Info

---

- Inner carton:
- Outer Carton: 10
- EAN Barcode: 5410329421342
- UPC Barcode:
- Packaging:

(C) 2005 Velleman Components N.V.  
[ [Disclaimer](#) ]