

Search Product:

Submit

[[Advanced](#)]

- ? [Adapters & power supplies](#)
- ? [Batteries & chargers](#)
- ? [Cables & accessories](#)
- ? [Connectors](#)
- ? [Consumer products & pc acc.](#)
- ? [Electronic components](#)
- ? [High-q tools & dmm's](#)
- ? [Led products & lamps](#)
- ? [Light products](#)
- ? [Loudspeakers & pa systems](#)
- ? [Perel tools](#)
- ? [Security products](#)
- ? [Velleman kits & oscilloscopes](#)

[ROHS Info](#)

[HIGH-Q TOOLS & DMM'S](#) > [SPECIAL METERS](#) > [DISTANCEMETERS](#) >



ULTRASONIC DISTANCE METER + LASER

Order Code: VTUSD3



Features

- ? large multifunctional LCD display with white backlight
- ? measures in Imperial / metric
- ? calculates the area and volume
- ? 5 memory groups for storing measurements
- ? laser pointer for increased accuracy
- ? auto / manual shutdown
- ? alarm function for wrong readings
- ? with carrying pouch

Specifications

- ? range: 1.64' to 52.48'
- ? accuracy: $\pm 1\% + 1$ digit
- ? laser:
 - ? <1 mW class 2
 - ? range: 130 ft
 - ? wavelength: 670nm
- ? response time: 2 sec
- ? operating current: <60mA
- ? operating temperature: 32°F ~ 104°F
- ? power supply: 1 x 9V 6LR61C battery (incl.)
- ? dimensions: 1" x 3 11/32" x 2 3/4"
- ? weight: 6.77oz

Files

- ? [EN- FR- NL- ES- DE](#)

Stock Info

- ? Inner carton:
- ? Outer Carton: 40
- ? EAN Barcode:
- ? Packaging: