

222-412 Item no.:

Product description: Compact connector 2-conductor terminal blocks with levers

max. continuous service temperature 85°C





Produkt kann von Bild abweichen / product may differ

Packing unit 1000 10*100 pieces

RoHS compliant

Product group 7 (Push Wire Conn.) Cross section [mm²] 0.08 - 2.5 mm² Cross section [AWG] 28 - 14 AWG

Wiring method s + f-st

CAGE CLAMP®CONNECTION Connection method

1 von 4

Cross section [mm²] 0.08 - 4 mm² Cross section [AWG] 28 - 12 AWG

Wiring method Measured voltage EN 400 V

Measured shock voltage 4 kV 2 Pollution degree Current intensity EN 32 A Weight 3.072 g

Color grey Wiring type Side-entry No. of connection Points 2

No. of potentials Height 14.5 mm Height 0.571 in

Width	12.4 mm
Width	0.488 in
Depth	20.5 mm



Depth0.807 inStrip length from9 mmStrip length to10 mmStrip length0.37 inCustoms Tariff No.85369010Country of OriginDeutschland



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
222-412	ABS	10-HN17750340X	450	32	0,5-4
222-412	cULus listed	E69654	600	20	28-12
222-412	ENEC15	DK140137-01	450	32	0,5-4
222-412	PSE	JET0695-43040-1001	600	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected