
Item no.: 283-601
Product description: 2-CONDUCTOR THROUGH TERMINAL BLOCK; LATERAL MARKING; for DIN 35 rail; FRONT-ENTRY; CAGE CLAMP®CONNECTION; HORIZONTAL TYPE



Packing unit 25 pieces

Product group	1 (Rail Mounted Terminal Blocks)
Cross section from [mm ²]	0,2 mm ²
Cross section to [mm ²]	16 mm ²
Cross section from [AWG]	24 AWG
Cross section to [AWG]	6 AWG
Connection method	CAGE CLAMP®CONNECTION
Diameter from	0 mm
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	76 A
Weight	31,72 g
Color	grey
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	1
Height	37,5 mm
Height	1,48 in
Width	12 mm
Width	0,472 in
Depth	80 mm
Depth	3,15 in



Strip length from	16 mm
Strip length to	17 mm
Strip length	0,65 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
283-601	ABS	05-HG476175/1-PDA	800	76	16
283-601	BV	07436/Co	800	76	16
283-601	CCA	NL5917	800	76	16
283-601	CSA	154112-1536072	600	80	24-6
283-601	DEMKO	79928	750		16
283-601	DNV	E7570	800	76	16
283-601	GL	17295-00HH	800	76	16
283-601	KEMA	2082859.12	800	76	16
283-601	KR	HMB05880-EL001	800	85	16
283-601	LR	91/20112(E5)	800	76	16
283-601	PRS	TE/1718/880590/08	800	76	16
283-601	RMR	11130002	800	76	16
283-601	UR	E45172	600	65	24-6

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected