
Accessories

Manuals, GSD and EDS Files, Marking Accessories, Mounting Accessories





Description		
Manuals:	for fieldbus couplers/controllers and ECO fieldbus couplers:	Available in German and English on the Internet at
	PROFINET, PROFIBUS, ETHERNET, DeviceNet, CANopen, ETHERNET	www.wago.com or as DVD AUTOMATION Tools and Docs
	Powerlink, MODBUS, INTERBUS, CC-Link, Firewire, CAL, Telecontrol,	0888-0412/xxxx-0101
	II/O-LIGHTBUS, KNX IP, BACnet, LON, Peer to Peer;	
	for I/O modules (digital input, digital output, analog input,	
	analog output, specialty modules, system modules,	
	Ex i, PROFIsafe)	
GSD and EDS files:	available for the fieldbus system PROFIBUS, DeviceNet and CANopen	









Description		Item no.	Pack. unit
Marker cards for group marking carrier	sheet DIN A4 (160 cards)	750-100	1 sheet
Miniature WSB quick marking system			
	plain	248-501	5 cards
	yellow	248-501/000-002	5 cards
	red	248-501/000-005	5 cards
	blue	248-501/000-006	5 cards
	gray	248-501/000-007	5 cards
	orange	248-501/000-012	5 cards
	light green	248-501/000-017	5 cards
	green	248-501/000-023	5 cards
	violet	248-501/000-024	5 cards
End stop, for DIN 35 rail	6 mm/0.236 in wide	249-116	100 (4x25
End stop, for DIN 35 rail	10 mm/0.394 in wide	249-117	50 (2x25)
Communication cable		750-920	1
Screwdriver with partially insulated shaft	Type 1, blade 2.5 x 0.4 mm / 0.098 x 0.016 in	210-619	1
Screwdriver with partially insulated shaft	Type 2, blade 3.5 x 0.5 mm / 0.137 x 0.020 in	210-620	1

Hansastr. 27 • D-32423 Minden Fax: +49(0)571/887-169 www.wago.com

Accessories

Miniature WSB Quick Marking System

Description		Item no.	Pack. unit
Miniature WSB quick marking system,			
Marking per card:			
0 V	100 x blue	247-506/000-006	5 cards
0 V	100 x white	247-506	5 cards
-	100 x blue	247-507/000-006	5 cards
-	100 x white	247-507	5 cards
24 V	100 x red	247-508/000-005	5 cards
24 V	100 x white	247-508	5 cards
+	100 x red	247-509/000-005	5 cards
+	100 x white	247-509	5 cards
(b)	100 x light green	247-552/000-017	5 cards
(100 x white	247-552	5 cards
PE	100 x light green	248-578/000-017	5 cards
PE	100 x white	248-578	5 cards
A0 A1 A8 A9	10 x white	247-510	5 cards
EO E1 E8 E9	10 x white	247-511	5 cards
X0 X1 X8 X9	10 x white	247-512	5 cards
0 to 09	10 x white	247-513	5 cards
10 to 19	10 x white	247-514	5 cards
20 to 29	10 x white	247-514	5 cards
30 to 39	10 x white	247-515	5 cards
40 to 49	10 x white	247-510	5 cards
50 to 59	10 x white	247-517	5 cards
60 to 69	10 x white	247-519	5 cards
70 to 79	10 x white	247-520	5 cards
80 to 89	10 x white	247-521	5 cards
90 to 99	10 x white	247-522	5 cards
00 to 49	2 x white	247-523	5 cards
50 to 99	2 x white	247-524	5 cards
100 to 149	2 x white	247-525	5 cards
150 to 199	2 x white	247-526	5 cards
200 to 249	2 x white	247-527	5 cards
250 to 299	2 x white	247-528	5 cards
300 to 349	2 x white	247-529	5 cards
350 to 399	2 x white	247-530	5 cards
400 to 449	2 x white	247-531	5 cards
450 to 499	2 x white	247-532	5 cards
500 to 549	2 x white	247-533	5 cards
550 to 599	2 x white	247-534	5 cards
600 to 649	2 x white	247-535	5 cards
650 to 699	2 x white	247-536	5 cards
700 to 749	2 x white	247-537	5 cards
750 to 799	2 x white	247-538	5 cards
800 to 849	2 x white	247-539	5 cards
850 to 899	2 x white	247-540	5 cards
900 to 949	2 x white	247-541	5 cards
950 to 999	2 x white	247-542	5 cards
.0 to .7 / plain	10 x /20 x white	247-543	5 cards
.0 to .7 /-	10 x / 20 x white	247-544	5 cards
.0 to .7 /-	10 x / 20 x blue	247-544/000-006	5 cards
.0 to .7 /+	10 x / 20 x white	247-545	5 cards
.0 to .7 /+	10 x / 20 x willie 10 x / 20 x red	247-545/000-005	5 cards
.0 to .7 /N	10 x / 20 x red 10 x / 20 x white	247-546	5 cards
•	•		
.0 to .7 /N .0 to .7 /L	10 x /20 x blue 10 x /20 x white	247-546/000-006 247-547	5 cards 5 cards

