


Item no.: 231-313/026-000
 Product description: FEMALE CONNECTOR 13 POLE PIN SPACING 5.08 MM / 0.2 IN WITH CODING FINGERS WITH INTEGRATED FIXING FLANGES



Produkt kann von Bild abweichen / product may differ

Packing unit 25 pieces

RoHS compliant

Product group	3 (Multi Conn. System)
Weight	23.65 g
Color	orange
No. of connection Points	13
No. of potentials	13
pole count	13
Height	14.3 mm
Height	0.563 in
Width	67.54 mm
Width	2.659 in
Depth	26.45 mm
Depth	1.041 in
Pin spacing from	5.08 mm
Pin spacing from	0.2 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV
Current intensity EN	16 A

Pollution degree	2
Measured voltage EN	630 V
Measured shock voltage	4 kV
Current intensity EN	16 A



Connection method	CAGE CLAMP® CONNECTION
Cross section [mm ²]	0.08 - 2.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.08 - 2.5 mm ²
Wiring method	fine-stranded
Cross section [mm ²]	0.25 - 1.5 mm ²
Wiring method	fine-stranded (with ferrule and plastic collar)
Cross section [mm ²]	0.25 - 2.5 mm ²
Wiring method	fine-stranded (with ferrule, without plastic collar)
Cross section [AWG]	28 - 12 AWG
Strip length from	8 mm
Strip length to	9 mm
Material group	I
Contact material	Copper base alloy
Contact surface	tin-plated
xxx-xxx/035-000	Strain relief plate 50 mm



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
231-313/026-000	BV	11915/A0	400	16	2,5
231-313/026-000	CCA	5764	250	16	0,08-2,5
231-313/026-000	CSA	154112-1466354	300	15	22-12
231-313/026-000	KEMA	2083746.02	250	16	0,08-2,5
231-313/026-000	KR	HMB05880-EL003	250/400/600	12/16	2,5
231-313/026-000	UR	E45171	600	15	28-12
231-313/026-000	UR	E45172	300	15	22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected