


[English](#) [日本語](#)
Electronics
a vital part of your world
**Find
Answers:**

Monday, 7 November, 2005

CATALOG

Cross Reference

[Competitive Products](#)
[Military Spec P/Ns](#)
[Tyco Brand P/Ns](#)

Part Number Search

Document Search

Product Type Search

Product Family Search

Alphabetical Search

RoHS/ELV Compliance & Alternates

CAD Model Search

Brand Search

Tool Search

Multiple Part Comparison

Lead Free Solutions

Help/Glossary

[Home](#)

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Soft Shell Connectors
↳ 5mm (.197") Centerline, 600 V, 14 A max. (Metrimate)
AMP 207378-1  Active
Not ELV or RoHS Compliant
(Corporate P/N: 207378-1)
Search for Compliant (RoHS/ELV)
Alternates
CAD Geometry | Search for Parts

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ✦ General Info ✦ Sales Info ✦ Assembly Subcontractors 	<ul style="list-style-type: none"> ✦ Pricing & Availability 	<ul style="list-style-type: none"> ✦ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)
Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	Not ELV/ RoHS compliant
Lead Free Solder Processes:	Wave solder capable to 240°C, Wave solder capable to 265°C
Product Type:	Header
Connector Configuration:	In-Line

Other Properties:

Contact Mating Area Plating:	Tin
Contact Material:	Copper Alloy
PCB Retention Method Feature:	Mounting Holes
Voltage (VAC):	600
Current Rating (Amps.):	14
Housing Material:	Thermoplastic
Housing Color:	Red
Housing Flammability Rating:	UL 94V-0

Number of Positions:	6
Gender:	Pin
Coaxial Socket:	Without
Keyed:	No
Mount:	Printed Circuit Board
PCB Mount Angle:	Right Angle
Mounting Ears:	With
Centerline (mm [in]):	5.00 [0.197]
Post Type:	Solder Post
Termination Post Length (mm [in]):	4.88 [0.192]
Mating Connector Lock:	Without
Jackscrew:	Without
8/32 Insert:	No
PCB Retention Feature:	Yes

Packaging Quantity:	40
Comment:	Pin and socket headers do not mate.

[Copyright and Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]