





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/26/18	
A		UPDATE SPEC.	2/18/23	WX/LL1



RECOMMENDED PCB LAYOUT



Poles: 01 thru 15

SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Black

Cover: PC, rated UL 94V-2

Contacts: Copper Alloy, Tin plated

Screw: M5 Steel, Zinc plated

Electrical:

Voltage rating: 600 V

Current rating: 65 A

Contact resistance: 20 mohms

Insulation resistance: 1000 Mohms / DC500V

Dielectric withstanding voltage: 2,200 VAC for 1 minute

Mechanical:

Wire Range: 14~6 AWG

Torque: 2.5Nm/25.0lb.in

Temperature Rating:

-40°C to +130°C

Environmental:

Lead free, RoHS compliant.



linear dimension (Tolerances Standard)								—	∇	⊥
variable range	to 6	over 6 to 10	over 10 to 30	over 30 to 60	over 60 to 100	over 100 to 160	over 160 to 200	to 10	over 10 to 100	over 100 to 200
tolerance	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±1.60	0.10	0.30	0.60

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ±.10	ØX ±.10
.XX ±.020	ØXX ±.015
.XXX ±.015	ØXXX ±.010

DRAWN	AY	11/26/18
CHECKED	AC	11/26/18
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE		TERMINAL BLOCK, .630 [16.00] PITCH W/ SNAP ON CLEAR COVER	
SIZE	PART NO.	TBU-XX-W3-CC	REV. A
REF:	S00067C	SCALE: NTS	SHEET 1 OF 1