






APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/26/18	



RECOMMENDED MOUNTING CUT-OUT



Poles: 02 thru 15

SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy, Tin plated

Screw: M4 Steel

Electrical:

Voltage rating: 300 V

Current rating: 30 A

Dielectric withstanding voltage: 2,000 VAC for 1 minute

Mechanical:

Wire Range: 22~10 AWG

Torque: 1.8 (N.m)

Temperature Rating:

Operating temperature: -40°C to +130°C

Environmental:

Lead free, RoHS compliant.



linear dimension (Tolerances Standard)								—	∇	⊥
variable	to	over	over	over	over	over	over		over	over
range	6	6 to 10	10 to 30	30 to 60	60 to 100	100 to 160	160 to	to 10	to 100	to 100
tolerance	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±1.60	0.10	0.30	0.60

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE MILLIMETERS
 TOLERANCES: EXCEPT AS NOTED

SEE CHART

APPROVALS		DATE
DRAWN	AY	11/26/18
CHECKED	AC	11/26/18
APPROVED		

ADAM
TECH
 INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE			
TERMINAL BLOCK, .433 [11.00] PITCH			
SIZE X	PART NO. TBU-XX-W1	REV. -	
REF: S00067C	SCALE: NTS	SHEET 1 OF 1	