



Product: [9222](#)

50Ω Triax RG-58A/U Type, #20, PO, TC Braids, PVC Jkt

Product Description

50 Ohm Triax RG-58A/U Type, 20 AWG stranded (7x28) .037" tinned copper conductor, polyethylene insulation, double tinned copper braid shields (95% coverage), PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	Analog video, Composite Video, Video Distribution
------------------------	---

Construction Details

RG Type:	58
----------	----

Conductor

Element	No. of Elements	Size	Stranding	Nom. Diameter	Material
Coax(es)	1	20 AWG	7x28	0.038 in	TC - Tinned Copper

Insulation

Element	Material	Nom. Insulation Diameter	Color Code
Coax(es)	PE - Polyethylene	0.12 in (3.0 mm)	White

Inner Shield

Element	Layer	Shield Type	Material	Coverage
Coax(es)	1	Braid	Tinned Copper (TC)	95%

Inner Jacket

Material	Nom. Diameter
PE - Polyethylene	0.177 in (4.50 mm)

Outer Shield

Layer	Outer Shield Type	Material	Coverage
1	Braid	Tinned Copper (TC)	95%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.241 in (6.12 mm)

Electrical Characteristics

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.5 dB/100ft
10 MHz	1.5 dB/100ft
50 MHz	3.3 dB/100ft
100 MHz	4.9 dB/100ft
200 MHz	7.2 dB/100ft
400 MHz	12 dB/100ft
500 MHz	14 dB/100ft

700 MHz	18 dB/100ft
900 MHz	22 dB/100ft
1000 MHz	24 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Delay Skew
9.5 Ohm/1000ft	4.7 Ohm/1000ft (15 Ohm/km)	4.3 Ohm/1000ft (14 Ohm/km)	30.8 pF/ft (101 pF/m)	50 Ohm	66%	66 ns/100m

Voltage

Voltage Rating
1400 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-40°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
2.41 in (61.2 mm)	2.41 in (61.2 mm)

Max. Pull Tension:	92 lbs (42 kg)
Bulk Cable Weight:	39 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Indoor
CPR Compliance:	CPR Euroclass: Fca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

History

Update and Revision:	Revision Number: 0.478 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9222 004100	Yellow	Reel	100 ft	612825225430	
9222 004500	Yellow	Reel	500 ft	612825225447	C
9222 004U500	Yellow	UnReel	500 ft	612825225423	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.