



Product: [REVConnect Dust Caps for Jacks](#) 

REVConnect Dust Cover Caps for Jacks

Product Description

REVConnect Dust Caps for Jacks are available in several colors in a bulk pack of 24.

Technical Specifications

Physical Characteristics (Overall)

Height:	0.634 in
Width:	0.571 in
Depth:	0.181
Packaging:	24 covers bulk packaged in a cardboard box.
Weight:	0.001 lbs

Connectors

Materials

Material
Plastic

Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Mechanical Characteristics

Footprint/Type:	REVConnect
-----------------	------------

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
MII Order #39 (China RoHS):	EUP 50

Related Part Numbers

Related Parts:	Compatible with Belden's REVConnect jacks
----------------	---

Variants

Item #	Color	Packaging	UPC
RVUDCAL-B24	Almond	24 covers bulk packaged in a cardboard box.	611589205368
RVUDCBK-B24	Black	24 covers bulk packaged in a cardboard box.	611589205382
RVUDCBL-B24	Blue	24 covers bulk packaged in a cardboard box.	611589205450
RVUDCBR-B24	Brown	24 covers bulk packaged in a cardboard box.	611589205405
RVUDCGY-B24	Gray	24 covers bulk packaged in a cardboard box.	611589205351

RVUDCGN-B24	Green	24 covers bulk packaged in a cardboard box.	611589205443
RVUDCIV-B24	Ivory	24 covers bulk packaged in a cardboard box.	611589205399
RVUDCOR-B24	Orange	24 covers bulk packaged in a cardboard box.	611589205429
RVUDCPR-B24	Purple	24 covers bulk packaged in a cardboard box.	611589205467
RVUDCRD-B24	Red	24 covers bulk packaged in a cardboard box.	611589205412
RVUDCEW-B24	White	24 covers bulk packaged in a cardboard box.	611589205375
RVUDCYL-B24	Yellow	24 covers bulk packaged in a cardboard box.	611589205436

History

Update and Revision:	Revision Number: 0.166 Revision Date: 03-04-2023
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.