

Specifications

Photo is representative

Eaton STS321150U332

Eaton TVS diode ESD supp. SOD-323 size, 15 op. voltage, 330 pF, 30 kV, Unidirectional

General specifications

PRODUCT NAME	Eaton TVS diode ESD suppressor
CATALOG NUMBER	STS321150U332
UPC	051712772112
PRODUCT LENGTH/DEPTH	2.75 mm
PRODUCT HEIGHT	1 mm
PRODUCT WIDTH	1.4 mm
PRODUCT WEIGHT	0.00588 g
COMPLIANCES	RoHS Compliant

Voltage, current and power ratings

VOLTAGE RATING	15 V
-----------------------	------

CLAMPING VOLTAGE	30
-------------------------	----

Package size, operating temperature, ESD rating

CAPACITANCE	330
--------------------	-----

ESD WITHSTAND - AIR	30
----------------------------	----

ESD WITHSTAND - CONTACT	30
--------------------------------	----

OPERATING TEMPERATURE - MIN	-55 °C
------------------------------------	--------

OPERATING TEMPERATURE - MAX	125 °C
------------------------------------	--------

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton sts32xxxxxxx TVS diode ESD suppressor data sheet](#)

[Eaton Specification Sheet - STS321150U332](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

