

Specifications

Eaton E10T215AS

Eaton E10 toggle switch, Two-pole, ON, None, OFF, 0.563 inch lever, Screw, Single-throw, 15A at 125 Vac, 10A at 250 Vac, 3/4 hp at 50 Vac, 0.47 inch bushing

General specifications

PRODUCT NAME	Eaton E10 toggle switch
CATALOG NUMBER	E10T215AS
UPC	782113698236
PRODUCT LENGTH/DEPTH	0.8 in
PRODUCT HEIGHT	2.1 in
PRODUCT WIDTH	0.7 in
PRODUCT WEIGHT	0.07 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Recognized CSA Certified
GLOBAL CATALOG	E10T215AS

Product specifications

TYPE	Toggle Switch
BUSHING LENGTH	0.47 inch bushing
NUMBER OF POLES	Two-pole
LEVER LENGTH	0.563 in
TERMINALS	Screw
THROW TYPE	Single-throw
RATING	15 A at 125 Vac, 10 A at 250 Vac, 1/2 hp at 50 Vac
SERIES	E10
NUMBER OF POSITIONS	ON, NONE, OFF

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - E10T215AS](#)

WARRANTY GUIDES

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

