

Specifications

Eaton E22KB62

Eaton E22 Pushbutton , Non-metallic Heavy-Duty, Cam 2, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, 22.5 mm, Two-position, Key, Left only, Black bezel, 45° Throw

General specifications

PRODUCT NAME	Eaton E22 pushbutton
CATALOG NUMBER	E22KB62
UPC	782113802749
PRODUCT LENGTH/DEPTH	2.5 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	0.14 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	CE Marked
CERTIFICATIONS	UL 508 CSA Certified IEC 947-5-1 MTTA Lloyd's Register Certified
CATALOG NOTES	Key Removal from Maintained Position Only. Will accept a maximum of 2 contact blocks (4 circuits) with supplied 3-way mounting adapter. Optional 5-way adapter will accept a maximum of 5 contact blocks (10 circuits)
GLOBAL CATALOG	E22KB62

Product specifications

TYPE	22.5 mm, Non-metallic Heavy-Duty
BEZEL	Black
CAM CODE	Cam 2
KEY REMOVAL POSITION	Left only
ENCLOSURE	NEMA 13 NEMA 4X NEMA 12 NEMA 3 NEMA 4 NEMA 3R
ACTUATOR	Key operated
THROW TYPE	45 °
ILLUMINATION	Non-illuminated
NUMBER OF POSITIONS	2
SERIES	E22

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet -
E22KB62](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

