

Product designation			LED elements steady light base mount on LPZ control station LPXLPB	
Product type designation				
General characteristics				
Colour			Red	
Electrical characteristics				
Rated frequency			Hz	50-60
Supply voltage (AC)			V	12...30
Operations				
Electrical life			hours	100000
Mechanical features				
Conductor section				
		AWG/kcmil conductor section		
		max	14	
		IEC		
		max	mm²	1 or 2 / 2.5
Mounting adapter				
Weight			g	16
Ambient conditions				
Temperature				
		Operating temperature		
		min	°C	-25
		max	°C	+70
		Storage temperature		
		min	°C	-40
		max	°C	+85
Dimensions				
Wiring diagrams				
Certifications and compliance				
Compliance				
		CSA C22.2 n° 14		
		IEC/EN/BS 60947-1		
		IEC/EN/BS 60947-5-1		
		UL508		
Certificates				
		CCC		
		cULus		
		EAC		
		RINA		
		UL		
ETIM classification				
ETIM 8.0			EC000204 - Lamp holder block for control circuit devices	