






MDC (M12) Series Cordsets

4 Conductor MDC Series Cordsets, 22AWG



Straight Female Cordsets | 300 Volt, 4 amps | IP69 Rating



Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MDC-4FP-** (Yellow) MDC-4FP-**-B (Black)	PVC AWM 4 X 22 AWG 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC	1. Brown 2. White 3. Blue 4. Black 5. Not Used	 M12 x 1
	MDCM-4FP-**	Yellow PVC AWM With Foil Shield 4 X 22 AWG 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC Foil Shield		
	MDCM-4FSP-**	Yellow PVC AWM With Foil Shield 4 X 22 AWG 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC Foil Shield to the Coupling Nut		
	MDCP-4FP-**	Yellow PUR AWM 4 X 22 AWG 300V, 4A -40°C to +80°C 5mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
	MDCW-4FP-**	Yellow TPE AWM 4 X 22 AWG 300V, 4A -40°C to +80°C 5mm OD	Weld Slag Resistant TPE		
	MDCWF-4FP-**	Black TPE AWM 4 X 22 AWG 300V, 4A -40°C to +80°C 5mm OD	Hi-Flex Weld Slag Resistant TPE		
	MDCPQ-4FP-**	Yellow PUR AWM 4 X 22 AWG 300V, 4A -40°C to +80°C 5mm OD	Coiled Oil and Cutting Fluid Resistant Cut Resistant PUR		

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

2~5 Pole females will have all 5 contact holes in the connector.

Black and gray cables are available on some versions, please consult the factory.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "SS" suffix. (e.g. MDC-4FP-1M becomes MDC-4FP-1M-SS)

H

Micro-DC (M12) Series Cordsets