





MDC (M12) Series Cordsets

4 Conductor MDC Series Cordsets, 18/22AWG



Double Ended Cordsets | Straight | 300 Volt, 4 amps | IP69 Rating




Male Faceview	Part Number	Cables	Features	Color Code	Female Faceview
 M12 x 1	MDC-4MFPX-**	Yellow PVC AWM 4 X 18 AWG 300V, 4A -40°C to +105°C 7.4mm OD	Industry Standard PVC	1. Brown 2. White 3. Blue 4. Black	 M12 x 1
	MDCP-4MFPX-**	Yellow PUR AWM 4 X 18 AWG 300V, 4A -40°C to +105°C 7.4mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
	MDC-4MFP-** (Yellow) MDC-4MFP-**-B (Black)	Yellow PVC AWM 4 X 22 AWG 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC		
	MDCM-4MFP-**	Yellow PVC AWM With Foil Shield 4 X 22 AWG 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC Foil Shield		
	MDCM-4MFPS-**	Yellow PVC AWM With Foil Shield 4 X 22 AWG 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC Foil Shield to the Coupling Nut		

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

4 Pole females will have all 5 contact holes in the connector.

Black and gray cables are available on some versions, please consult the factory.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "SS" suffix. (e.g. MDC-5MFPX-1M becomes MDCM-5MFPX-1M-SS)



Male - Female Extension