





MDC (M12) Series Cordsets

4 Conductor MDC Series Cordsets, 18AWG



Straight Male Cordsets | 300 Volt, 4 amps | IP69 Rating



Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MDC-4MPX-** (Yellow) MDC-4MPX-**-B (Black)	Yellow PVC AWM 4 X 18 AWG 300V, 4A -40°C to +105°C 7.4mm OD	Industry Standard PVC	1. Brown 2. White 3. Blue 4. Black	 M12x1
	MDCP-4MPX-**	Yellow PUR AWM 4 X 18 AWG 300V, 4A -40°C to +80°C 7.4mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
	MDCW-4MPX-**	Yellow TPE AWM 4 X 18 AWG 300V, 4A -40°C to +80°C 7.4mm OD	Weld Slag Resistant TPE		

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult the factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MDC-4MPX-1M becomes MDC-4MPX-1M-SS)

H

Micro-DC (M12) Series Cordsets