



1 1/8" MIN Series Size III Cordsets

9, 10 & 12 Conductor MIN Series Size III Cordsets, 16/18AWG



Straight Male Cordsets | 600V, 7/5A | 300V, 4A | IP69 Rating



MIN Series Size III Cordsets

Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MIN-9MP*-C011	Black PVC AWM 9 X 16 AWG 600V, 7A -40°C to +105°C 12.1mm OD	PVC TC-ER	North American 1. Orange 2. Blue 3. Red/Black 4. Green/Black 5. White 6. Red 7. Green/Yellow 8. White/Black 9. Black	 1 1/8"-16UN2
	MIN-9MPX*-	Yellow PVC AWM 9 X 18 AWG 300V, 4A -40°C to +105°C 9.1mm OD	Industry Standard PVC		
	MINP-9MPX*-	Yellow PUR AWM 9 X 18 AWG 300V, 4A -40°C to +80°C 9.1mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
	MIN-10MP*-C011	Black PVC AWM 10 X 16 AWG 600V, 7A -40°C to +105°C 14mm OD	PVC TC-ER	North American 1. Orange 2. Blue 3. White/Black 4. Red/Black 5. Green/Black 6. Orange/Black 7. Red 8. Green/Yellow 9. Black 10. White	 1 1/8"-16UN2
	MIN-10MPX*-	Yellow PVC AWM 10 X 18 AWG 300V, 4A -40°C to +105°C 10.1mm OD	Industry Standard PVC		
	MINP-10MPX*-	Yellow PUR AWM 10 X 18 AWG 300V, 4A -40°C to +80°C 10.1mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
	MIN-12MP*-C011	Black PVC AWM 12 X 16 AWG 600V, 5A -40°C to +105°C 14mm OD	PVC TC-ER	North American 1. Orange 2. Blue 3. White/Black 4. Red/Black 5. Green/Black 6. Orange/Black 7. Blue/Black 8. Black/White 9. Green/Yellow 10. Red 11. White 12. Black	 1 1/8"-16UN2
	MIN-12MPX*-	Yellow PVC AWM 12 X 18 AWG 300V, 4A -40°C to +105°C 10.5mm OD	Industry Standard PVC		
	MINP-12MPX*-	Yellow PUR AWM 12 X 18 AWG 300V, 4A -40°C to +80°C 10.5mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		

* Length in feet. Standard cable lengths are 3, 6, 12, 20, 30 & 50 feet. Consult factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "SS" suffix. (e.g. MIN-10MPX-3 becomes MIN-10MPX-3-SS)

For male threaded coupling nut replace "MPX" with "MPMX". (e.g. MIN-10MPX-3 becomes MIN-10MPMX-3)