



7/8" MIN Series Size I Cordsets

4 Conductor MIN Series Size I Cordsets, 16AWG



Straight Male Cordsets | 600 Volt, 10 amps | IP69 Rating

A

MIN Series Size I Cordsets



Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MIN-4MP-* (YELLOW)	PVC STOOW 4 X 16 AWG 600V, 10A -40°C to +105°C 10.8mm OD	Industry Standard PVC	North American 1. Black 2. White 3. Red 4. Green/Yellow	 7/8"-16UN2
	MIN-4MP-* (BLACK)	Yellow PVC STOOW With Foil Shield 4 X 16 AWG 600V, 10A -40°C to +105°C 10.8mm OD	Industry Standard PVC Foil Shield		

* Lengths in feet. Standard cable lengths are 3, 6, 12, 20, 30 & 50 feet. Consult factory for other lengths.
 Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "SS" suffix. (e.g. MIN-4MP-3 becomes MIN-4MP-3-SS)
 See Page A-33 for Armored Cordset options.

Male Thread Option

For male threaded coupling replace "MP" with "MPM".
 (e.g. MIN-4MP-3 becomes MINM-4MPM-3)

