



7/8" MIN Series Size I Cordsets

3, 4 & 5 Conductor MIN Series Size I Cordsets, 18AWG



Double Ended Cordsets | 300 Volt | IP69 Rating

A

MIN Series Size I Cordsets



Male Faceview	Part Number	Cables	Features	Color Code	Female Faceview
 7/8"-16UN2	MIN-3MFPX-* (YELLOW) MIN-3MFPX-*-B (BLACK)	PVC SJTOOW 3 X 18 AWG 300V, 10A -40°C to +105°C 8.5mm OD	Industry Standard PVC	North American 1. Green/Yellow 2. Black 3. White	 7/8"-16UN2
	MINE-3MFPX-**	PVC AWM 3 X 18 AWG 300V, 10A -40°C to +105°C 7.4mm OD	Industry Standard PVC Male Connector has Male Threads	European 1. Green/Yellow 2. Red/Black 3. Red/White	
 7/8"-16UN2	MIN-4MFPX-*	PVC AWM 4 X 18 AWG 300V, 8A -40°C to +105°C 7.4mm OD	Industry Standard PVC	North American 1. Black 2. White 3. Red 4. Green/Yellow	 7/8"-16UN2
 7/8"-16UN2	MINC-4MFPX-**	Yellow PVC AWM 4 X 18 AWG 300V, 8A -40°C to +105°C 7.4mm OD	Industry Standard PVC Male Connector has Male Threads	European Cenelec 1. Brown 2. White 3. Blue 4. Black	 7/8"-16UN2
	MINCP-4MFPX-**	Yellow PUR AWM 4 X 18 AWG 300V, 8A -40°C to +80°C 7.4mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR Male Connector has Male Threads		
	MINCW-4MFPX-**	Yellow TPE AWM 4 X 18 AWG 300V, 8A -40°C to +80°C 7.4mm OD	Weld Slag Resistant TPE Male Connector has Male Threads		
 7/8"-16UN2	MIN-5MFPX-* (YELLOW) MIN-5MFPX-*-B (BLACK)	PVC AWM 5 X 18 AWG 300V, 5.5A -40°C to +105°C 7.4mm OD	Industry Standard PVC	North American 1. White 2. Red 3. Green/Yellow 4. Orange 5. Black	 7/8"-16UN2
	MINP-5MFPX-*	Yellow PUR AWM 5 X 18 AWG 300V, 5.5A -40°C to +80°C 13.1mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
	MINE-5MFPX-**	PVC AWM 5 X 18 AWG 300V, 5.5A -40°C to +105°C 7.4mm OD	Industry Standard PVC Male Connector has Male Threads	European 1. Black 2. Blue 3. Green/Yellow 4. Brown 5. White	