



1 1/8" MIN Series Size III Cordsets

9 & 10 Conductor MIN Series Size III Cordsets, 16/18AWG



Double Ended Cordsets | 600V, 7A | 300V, 4A | IP69 Rating



MIN Series Size III Cordsets


Male Faceview	Part Number	Cables	Features	Color Code	Female Faceview
<p>1 1/8"-16UN2</p>	MIN-9MFP-*C011	Black PVC AWM 9 X 16 AWG 600V, 7A -40°C to +105°C 12.1mm OD	PVC TC-ER	North American 1. Orange 2. Blue 3. Red/Black 4. Green/Black 5. White 6. Red 7. Green/Yellow 8. White/Black 9. Black	<p>1 1/8"-16UN2</p>
	MIN-9MFPX-*	Yellow PVC AWM 9 X 18 AWG 300V, 4A -40°C to +105°C 9.2mm OD	Industry Standard PVC		
	MINP-9MFPX-*	Yellow PUR AWM 9 X 18 AWG 300V, 4A -40°C to +80°C 9.2mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
<p>1 1/8"-16UN2</p>	MIN-10MFP-*C011	Black PVC AWM 10 X 16 AWG 600V, 7A -40°C to +105°C 14mm OD	PVC TC-ER	North American 1. Orange 2. Blue 3. White/Black 4. Red/Black 5. Green/Black 6. Orange/Black 7. Red 8. Green/Yellow 9. Black 10. White	<p>1 1/8"-16UN2</p>
	MIN-10MFPX-*	Yellow PVC AWM 10 X 18 AWG 300V, 4A -40°C to +105°C 10.1 mm OD	Industry Standard PVC		
	MINP-10MFPX-*	Yellow PUR AWM 10 X 18 AWG 300V, 4A -40°C to +80°C 10.1mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		

* Length in feet. Standard cable lengths are 3, 6, 12, 20, 30 & 50 feet. Consult factory for other lengths.


Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MIN-10MFPX-3 becomes MIN-10MFPX-3-SS)

For male threaded coupling nut replace "MFP" with "MFPM". (e.g. MIN-10MFPX-3 becomes MIN-10MFPMX-3)

For available options for extension cables with right angle male and/or female ends, please consult the factory.



TC-ER Male - Female Extension



AWM Male - Female Extension