

BU-131

(Cast Aluminum Grounding Clip)



- Strong clamp pressure
- Perfect for grounding and/or bonding of drums, machinery, large and small containers, and personnel in areas containing flammables and dust.
- Will not twist
- Point-to-point connection to pierce paint
- Used for Static Electricity, good corrosion resistant
- Material:
 - Body – Aluminum
 - Tips – stainless steel
- Rating:
 - Amperage Rating: 10 Amps
 - Max Operating Temperature: 232°C (450°F)
- Dimensions:
 - 4.35" (110.5mm) long, 3.18" (80.75mm) height
 - Max width of 0.81" (20.57mm)
 - Points open up to 1"
 - 55 pound spring compression
 - Thread size: ¼ - 20